SKU: ZENOVAL6636-GCB

GOLD COMBINATION

TECHNICAL SPECIFICATIONS	
Drain	End drain
Pump Location(s): Select 2	Std. = Standard / Alt LF/RF Optional
Bath Weight (empty)	165 lbs
Gallons to Operate	66-84
ELECTRICAL SPECIFICATIONS	
Motor/Pump	(2) 115v 20AMP GFCI Circuits
Inline Stainless Steel Heater	(1) 115v 20AMP GFCI Circuit

BATHERS: 1	
INSTALLATION	
•	DECK (D)
•	UNDER MOUNT (U)
	ALCOVE (A)
	FREESTANDING (F)
	CLAWFOOT (L)
	PEDESTAL (P)
	PEDESTAL (P)



STANDARD FEATURES & ACCESSORIES for GOLD COMBINATION

JETS

30 Air & Water Massage Jets Back Massage System(s) (6 Jets) Sole Soother Jets Accumassage Back & Neck Jets ⊕ Ultra Flow Jets - ()-Classic Air Jets 🔿

PUMPS

1- 3.25 Hydropower 3-speed Pump 1.25 Air Power Variable Speed, Pulse & Wave heated Air Pump Quiet Pad Anti-Vibration Mounted Pump

HEATERS

Stainless Steel Electric Heater Warm Back Rest Tubing Zone

CONTROLS

Air Switch On/Off Control(s) For Hydro Pump & Chromatherapy Lighting Electronic Variable Speed Air Massage Control Automatic Purge & Dry Cycle Control 3 Speed Massage: High, Medium or Low

PURITY

HydroClean Water Purity System HydroCleanse

STANDARD ACCESSORIES

Grab Bar(s) - 2 on End Drain baths - White, Biscuit, Bone, Brushed Nickel, Polished Chrome

Chromatherapy Lighting

Deluxe Cable Drain - White, Biscuit, Bone, Brushed Nickel, Oil Rubbed Bronze, Polished Chrome,

Deluxe Cushion Pillow

F7 Level Base

FDA Recipe Non-Toxic Food & Beverage Grade Plumbing (primarily) 30 Point Quality Assurance Factory Test

REQUIREMENTS

Pump Locations: Select 2

Electrical: three 115v 20AMP GFCI Circuits Drain and Grab Bars: Select Color / Finish

Tub should not be supported by the lip in any way.


Level tub & screw or glue EZ Level adjustable legs to sub floor. **CUT OUT DIMENSIONS:**

OVALS: A template will be provided

RECTANGLES: Subtract 1" to 1.5" from length & width for hole cut out size


EZ CLEAN CAST ACRYLIC LIMITED LIFETIME WARRANTY






B X 6 Jet HTT® Back Massage System: N/A on Combo Series-Standard on Plat series

ⓒ SWarm Back Tubing Zone





Some standard & most alternate pump locations may stickout past perimeter of the bath 1"-3". NOTE: Graphics may not be to scale. Specifications and features are subject to change without notice and are ± .25". All final measurements should be taken from tub on site. Access 18"x 18" or larger is required for each pump. Consult your contractor for installation requirements.