**TECHNICAL SPECIFICATIONS** 

**ELECTRICAL SPECIFICATIONS** 

Pump Location(s): Select 1

Bath Weight (empty)

Gallons to Operate

Motor/Pump

Std. = Standard / Alt LF/RF Optional

(1) 115v 20AMP GFCI Circuits

End drain

180 lbs

72-90

BATHERS: 1	
INSTALLATION	
oxdot	DECK (D)
•	UNDER MOUNT (U)
•	ALCOVE (A)
	FREESTANDING (F)
	CLAWFOOT (L)
	PEDESTAL (P)

Jet & Control placement may vary



# STANDARD FEATURES & ACCESSORIES for GOLD AIR

#### **JETS**

Drain

18 EZ Clean™ Air Jets on Sidewall X

### **PUMPS**

1.25 Air Power Variable Speed, Pulse & Wave heated Air Pump Quiet Pad Anti-Vibration Mounted Pump

#### **HEATERS**

Warm Back Rest Tubing Zone

# **CONTROLS**

Air Switch On/Off Control(s) for mood lighting Variable Speed Air Massage Control Automatic Purge & Dry Cycle Control

#### **PURITY**

HydroCleanse

# STANDARD ACCESSORIES

Mood Light

Lift & Turn Drain - White, Biscuit, Bone, Brushed Nickel, Oil Rubbed Bronze, Polished Chrome

**Deluxe Cushion Pillow** 

EZ Level Adjustable Legs

FDA Recipe Non-Toxic Food & Beverage Grade Plumbing (primarily) 30 Point Quality Assurance Factory Test

#### REQUIREMENTS

Pump Locations: Select 1

Electrical: one 115v 20AMP GFCI Circuits

Drain: Select Color / Finish

Tub should not be supported by the lip in any way. Level tub & screw or glue EZ Level adjustable legs to sub floor.

CUT OUT DIMENSIONS:


**OVALS:** A template will be provided


**RECTANGLES:** Subtract 1" to 1.5" from length & width for hole

cut out size

EZ CLEAN CAST ACRYLIC LIMITED LIFETIME WARRANTY <sup>6</sup> TEXTURED FLOOR









INSTALLATION WILL NOT REQUIRE MORTAR BEDDING

- X HTT® Leg Therapy Air Massage System includes 10 Air Jets on the floor. Optional on Combo Plat and Combo Gold Series
- B X 6 Jet HTT® Back Massage System: N/A on Combo Series-Standard on Plat series
- **③ S** Warm Back Tubing Zone





Some standard & most alternate pump locations may stickout past perimeter of the bath 1"-3". NOTE: Graphics may not be to scale.

Specifications and features are subject to change without notice and are ± .25". All final measurements should be taken from tub on site.

Access 18"x 18" or larger is required for each pump. Consult your contractor for installation requirements.